

Garant
Through hole machine tap, uncoated, Type: 3/8-32

Order data

Order number	130030 3/8-32
GTIN	4062406034719
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 3 pcs.
 Special / custom-made product - return not possible
 Thread type: UNEF
 Tool material: HSS E
 Standard: DIN 371
 Threads per inch: 32
 Thread \varnothing : 9.525 mm
 Overall length L: 100 mm
 Shank \varnothing D_s: 10 mm
 Shank square \square : 8 mm
 Tapping hole \varnothing : 8.85 mm

Technical description

Overall length L	100 mm
Number of clamping slots	3
Shank square \square	8 mm
Tool material	HSS E
Thread depth	28.59 mm
Threads per inch	32
Standard	DIN 371

Tapping hole Ø	8.85 mm
Thread Ø	9.525 mm
Thread pitch	0.794 mm
Shank Ø D _s	10 mm
Number of cutting edges Z	3
Thread type	UNEF
Thread size	3/8-32 UNEF
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap