

Garant
Through hole machine tap, uncoated, Type: NO.10-32

Order data

| | |
|--------------|-----------------|
| Order number | 130030 NO.10-32 |
| GTIN | 4062406034429 |
| Item class | 10N |

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 3 pcs.
 Special / custom-made product - return not possible
 Thread type: UNF
 Tool material: HSS E
 Standard: DIN 371
 Threads per inch: 32
 Thread \varnothing : 4.83 mm
 Overall length L: 70 mm
 Shank \varnothing D_s: 6 mm
 Shank square \square : 4.9 mm
 Tapping hole \varnothing : 4.1 mm

Technical description

| | |
|------------------------------------|----------|
| Threads per inch | 32 |
| Overall length L | 70 mm |
| Thread depth | 14.49 mm |
| Shank \varnothing D _s | 6 mm |
| Tool material | HSS E |
| Number of cutting edges Z | 3 |
| Thread \varnothing | 4.83 mm |

| | |
|----------------------------------|--|
| Thread pitch | 0.794 mm |
| Shank square □ | 4.9 mm |
| Tapping hole Ø | 4.1 mm |
| Standard | DIN 371 |
| Number of clamping slots | 3 |
| Thread type | UNF |
| Thread size | 10-32 UNF |
| Coating | uncoated |
| Flank angle | 60 ° |
| Thread standard | ASME B1.1 |
| Tolerance class | 1B |
| Tolerance class | 2B +0.20 |
| Tolerance class | 2B +0.10 |
| Tolerance class | 3B |
| Tolerance class | 2B |
| Tolerance class | 2B +0.05 |
| Taper lead form | B |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for through holes |
| Cutting direction | right-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |