

Garant
Through hole machine tap, uncoated, Type: 13/16-16

Order data

Order number	130030 13/16-16
GTIN	4062406035228
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread Ø: 20.638 mm

Overall length L: 140 mm

Shank Ø D_s: 18 mm

Shank square □: 14.5 mm

Tapping hole Ø: 19.1 mm

Technical description

Thread Ø	20.638 mm
Number of cutting edges Z	3
Thread pitch	1.588 mm
Tool material	HSS E
Standard	DIN 376
Thread depth	41.3 mm
Number of clamping slots	3

Overall length L	140 mm
Threads per inch	16
Shank $\varnothing D_s$	18 mm
Shank square \square	14.5 mm
Tapping hole \varnothing	19.1 mm
Thread type	UN
Thread size	13/16-16 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap