

**Garant****Through hole machine tap, uncoated, Type: 9/16-16****Order data**

Order number	130030 9/16-16
GTIN	4062406034986
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days  
Minimum order quantity: 2 pcs.  
Special / custom-made product - return not possible  
Thread type: UN  
Tool material: HSS E  
Standard: DIN 376  
Threads per inch: 16  
Thread  $\varnothing$ : 14.29 mm  
Overall length L: 110 mm  
Shank  $\varnothing$  D<sub>s</sub>: 11 mm  
Shank square  $\square$ : 9 mm  
Tapping hole  $\varnothing$ : 12.8 mm

**Technical description**

Threads per inch	16
Overall length L	110 mm
Number of cutting edges Z	3
Standard	DIN 376
Thread depth	57.16 mm
Thread pitch	1.588 mm
Tapping hole $\varnothing$	12.8 mm

Tool material	HSS E
Shank square <input type="checkbox"/>	9 mm
Thread $\varnothing$	14.29 mm
Number of clamping slots	3
Shank $\varnothing D_s$	11 mm
Thread type	UN
Thread size	9/16-16 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap