

**Garant****Left-hand thread through hole machine tap, uncoated, Type: 13/16-20****Order data**

Order number	130031 13/16-20
GTIN	4062406037451
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNEF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread  $\varnothing$ : 20.638 mm

Overall length L: 140 mm

Shank  $\varnothing$  D<sub>s</sub>: 18 mmShank square  $\square$ : 14.5 mmTapping hole  $\varnothing$ : 19.6 mm**Technical description**

Thread depth	41.3 mm
Standard	DIN 376
Threads per inch	20
Number of cutting edges Z	3
Shank square $\square$	14.5 mm
Tool material	HSS E
Number of clamping slots	3

Tapping hole Ø	19.6 mm
Thread Ø	20.638 mm
Overall length L	140 mm
Thread pitch	1.27 mm
Shank Ø D <sub>s</sub>	18 mm
Thread type	UNEF-LH
Thread size	13/16-20 UNEF LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap