

**Garant**
**Through hole machine tap, uncoated, Type: 1.7/8-12**

**Order data**

Order number	130030 1.7/8-12
GTIN	4062406036331
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UN  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 12  
 Thread  $\varnothing$ : 47.625 mm  
 Overall length L: 250 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 36 mm  
 Shank square  $\square$ : 29 mm  
 Tapping hole  $\varnothing$ : 45.6 mm

**Technical description**

Standard	DIN 376
Thread pitch	2.117 mm
Number of clamping slots	4
Thread $\varnothing$	47.625 mm
Tapping hole $\varnothing$	45.6 mm
Shank $\varnothing$ D <sub>s</sub>	36 mm
Shank square $\square$	29 mm
Overall length L	250 mm

Threads per inch	12
Thread depth	95.25 mm
Number of cutting edges Z	4
Tool material	HSS E
Thread type	UN
Thread size	1.7/8-12 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap