

Garant
Through hole machine tap, uncoated, Type: 1.1/2-6

Order data

Order number	130030 1.1/2-6
GTIN	4062406035983
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UNC
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 6
 Thread \varnothing : 38.1 mm
 Overall length L: 200 mm
 Shank \varnothing D_s: 32 mm
 Shank square \square : 24 mm
 Tapping hole \varnothing : 33.7 mm

Technical description

Number of cutting edges Z	4
Tapping hole \varnothing	33.7 mm
Number of clamping slots	4
Thread pitch	4.233 mm
Tool material	HSS E
Standard	DIN 376
Shank square \square	24 mm
Threads per inch	6

Thread Ø	38.1 mm
Shank Ø D _s	32 mm
Thread depth	76.2 mm
Overall length L	200 mm
Thread type	UNC
Thread size	1.1/2-6 UNC
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap