

Garant
Through hole machine tap, uncoated, Type: 9/16-18

Order data

Order number	130030 9/16-18
GTIN	4062406034979
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNF
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 18
 Thread \varnothing : 14.29 mm
 Overall length L: 110 mm
 Shank \varnothing D_s: 11 mm
 Shank square \square : 9 mm
 Tapping hole \varnothing : 12.9 mm

Technical description

Tool material	HSS E
Standard	DIN 376
Thread pitch	1.411 mm
Number of cutting edges Z	3
Number of clamping slots	3
Shank \varnothing D _s	11 mm
Shank square \square	9 mm

Thread Ø	14.29 mm
Thread depth	57.16 mm
Overall length L	110 mm
Threads per inch	18
Tapping hole Ø	12.9 mm
Thread type	UNF
Thread size	9/16-18 UNF
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap