

Garant**Left-hand thread through hole machine tap, uncoated, Type: 5/8-11****Order data**

Order number	130031 5/8-11
GTIN	4062406037321
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNC-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 11

Thread \varnothing : 15.88 mm

Overall length L: 110 mm

Shank \varnothing D_s: 12 mmShank square \square : 9 mmTapping hole \varnothing : 13.53 mm**Technical description**

Standard	DIN 376
Shank square \square	9 mm
Thread depth	47.64 mm
Number of cutting edges Z	3
Number of clamping slots	3
Thread \varnothing	15.88 mm
Shank \varnothing D _s	12 mm

Overall length L	110 mm
Tapping hole Ø	13.53 mm
Tool material	HSS E
Threads per inch	11
Thread pitch	2.309 mm
Thread type	UNC-LH
Thread size	5/8-11 UNC LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap