

Garant**Left-hand thread through hole machine tap, uncoated, Type: 15/16-16****Order data**

Order number	130031 15/16-16
GTIN	4062406037581
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread Ø: 23.812 mm

Overall length L: 160 mm

Shank Ø D_s: 18 mm

Shank square □: 14.5 mm

Tapping hole Ø: 22.3 mm

Technical description

Number of clamping slots	3
Thread Ø	23.812 mm
Tapping hole Ø	22.3 mm
Thread pitch	1.588 mm
Standard	DIN 376
Tool material	HSS E
Shank square □	14.5 mm

Threads per inch	16
Overall length L	160 mm
Number of cutting edges Z	3
Thread depth	47.64 mm
Shank $\varnothing D_s$	18 mm
Thread type	UN-LH
Thread size	15/16-16 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap