

Garant**Through hole machine tap, uncoated, Type: 1.13/16-8****Order data**

Order number	130030 1.13/16-8
GTIN	4062406036287
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 8

Thread \varnothing : 46.037 mm

Overall length L: 250 mm

Shank \varnothing D_s: 36 mmShank square \square : 29 mmTapping hole \varnothing : 43 mm**Technical description**

Thread \varnothing	46.037 mm
Shank \varnothing D _s	36 mm
Tool material	HSS E
Standard	DIN 376
Number of cutting edges Z	4
Overall length L	250 mm
Thread pitch	3.175 mm

Tapping hole Ø	43 mm
Number of clamping slots	4
Thread depth	92 mm
Shank square □	29 mm
Threads per inch	8
Thread type	UN
Thread size	1.13/16-8 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap