

**Garant****Through hole machine tap, uncoated, Type: 5/8-16****Order data**

Order number	130030 5/8-16
GTIN	4062406035051
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread  $\varnothing$ : 15.88 mm

Overall length L: 110 mm

Shank  $\varnothing$  D<sub>s</sub>: 12 mmShank square  $\square$ : 9 mmTapping hole  $\varnothing$ : 14.4 mm**Technical description**

Shank $\varnothing$ D <sub>s</sub>	12 mm
Number of clamping slots	3
Tool material	HSS E
Thread $\varnothing$	15.88 mm
Thread depth	47.64 mm
Thread pitch	1.588 mm
Threads per inch	16

Tapping hole Ø	14.4 mm
Overall length L	110 mm
Number of cutting edges Z	3
Shank square □	9 mm
Standard	DIN 376
Thread type	UN
Thread size	5/8-16 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap