

Garant
Through hole machine tap, uncoated, Type: 1-24

Order data

Order number	130030 1-24
GTIN	4062406035372
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UNS
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 24
 Thread \varnothing : 25.4 mm
 Overall length L: 160 mm
 Shank \varnothing D_s: 20 mm
 Shank square \square : 16 mm
 Tapping hole \varnothing : 24.5 mm

Technical description

Shank \varnothing D _s	20 mm
Shank square \square	16 mm
Threads per inch	24
Number of clamping slots	4
Standard	DIN 376
Thread pitch	1.058 mm
Number of cutting edges Z	4

Tool material	HSS E
Overall length L	160 mm
Thread Ø	25.4 mm
Thread depth	76.2 mm
Tapping hole Ø	24.5 mm
Thread type	UNS
Thread size	1-24 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap