

**Garant**
**Spiral flute machine tap, TiN, MF: M16X0,35**

**Order data**

Order number	130015 M16X0,35
GTIN	4062406019136
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

**Technical description**

Thread pitch	0.35 mm
Number of clamping slots	3
Number of cutting edges Z	3
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX

Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread Ø	16 mm
Shank Ø D <sub>s</sub>	12 mm
Tool material	HSS E
Overall length L	110 mm
Thread depth	40 mm
Tapping hole Ø	15.65 mm
Shank square □	9 mm
Standard	DIN 376
Thread type	M
Thread size	M16×0.35
Coating	TiN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap