

Garant
Through hole machine tap, uncoated, Type: 1.3/4-14

Order data

Order number	130030 1.3/4-14
GTIN	4062406036201
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UNS
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 14
 Thread \varnothing : 44.45 mm
 Overall length L: 220 mm
 Shank \varnothing D_s: 36 mm
 Shank square □: 29 mm
 Tapping hole \varnothing : 42.85 mm

Technical description

Tapping hole \varnothing	42.85 mm
Threads per inch	14
Thread \varnothing	44.45 mm
Overall length L	220 mm
Standard	DIN 376
Shank \varnothing D _s	36 mm
Thread pitch	1.814 mm
Number of clamping slots	4

Thread depth	88.9 mm
Tool material	HSS E
Number of cutting edges Z	4
Shank square □	29 mm
Thread type	UNS
Thread size	1.3/4-14 UNS
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap