

Garant
Left-hand thread through hole machine tap, uncoated, Type: 1/4-24

Order data

Order number	130031 1/4-24
GTIN	4062406036836
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 24

Thread \varnothing : 6.35 mm

Overall length L: 80 mm

Shank \varnothing D_s: 7 mm

Shank square \square : 5.5 mm

Tapping hole \varnothing : 5.35 mm

Technical description

Shank \varnothing D _s	7 mm
Standard	DIN 371
Number of cutting edges Z	3
Thread pitch	1.058 mm
Tapping hole \varnothing	5.35 mm
Overall length L	80 mm
Shank square \square	5.5 mm

Thread depth	19.05 mm
Threads per inch	24
Number of clamping slots	3
Tool material	HSS E
Thread Ø	6.35 mm
Thread type	UNS-LH
Thread size	1/4-24 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap