


Garant**Left-hand thread through hole machine tap, uncoated, Type: 1.5/16-18****Order data**

Order number	130031 1.5/16-18
GTIN	4062406037970
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNEF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 18

Thread \varnothing : 33.338 mm

Overall length L: 200 mm

Shank \varnothing D_s: 28 mmShank square \square : 22 mmTapping hole \varnothing : 32.1 mm**Technical description**

Thread pitch	1.411 mm
Standard	DIN 376
Tapping hole \varnothing	32.1 mm
Overall length L	200 mm
Number of cutting edges Z	4
Thread \varnothing	33.338 mm
Shank square \square	22 mm

Threads per inch	18
Shank $\varnothing D_s$	28 mm
Thread depth	66.69 mm
Number of clamping slots	4
Tool material	HSS E
Thread type	UNEF-LH
Thread size	1.5/16-18 UNEF LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap