

Garant
Through hole machine tap, uncoated, Type: 1.7/16-16

Order data

Order number	130030 1.7/16-16
GTIN	4062406035877
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UN
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 16
 Thread \varnothing : 36.512 mm
 Overall length L: 200 mm
 Shank \varnothing D_s: 28 mm
 Shank square \square : 22 mm
 Tapping hole \varnothing : 35 mm

Technical description

Number of cutting edges Z	4
Shank \varnothing D _s	28 mm
Number of clamping slots	4
Thread \varnothing	36.512 mm
Standard	DIN 376
Threads per inch	16
Shank square \square	22 mm

Thread pitch	1.588 mm
Tapping hole Ø	35 mm
Thread depth	73 mm
Overall length L	200 mm
Tool material	HSS E
Thread type	UN
Thread size	1.7/16-16 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap