

**Garant**
**Through hole machine tap, uncoated, Type: 1.15/16-16**

**Order data**

Order number	130030 1.15/16-16
GTIN	4062406036379
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UN  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 16  
 Thread  $\varnothing$ : 49.212 mm  
 Overall length L: 250 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 40 mm  
 Shank square  $\square$ : 32 mm  
 Tapping hole  $\varnothing$ : 47.7 mm

**Technical description**

Number of cutting edges Z	4
Number of clamping slots	4
Shank square $\square$	32 mm
Tool material	HSS E
Thread pitch	1.588 mm
Thread $\varnothing$	49.212 mm
Threads per inch	16

Thread depth	98.4 mm
Overall length L	250 mm
Tapping hole Ø	47.7 mm
Shank Ø D <sub>s</sub>	40 mm
Standard	DIN 376
Thread type	UN
Thread size	1.15/16-16 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap