

Garant**Through hole machine tap, uncoated, Type: 11/16-16****Order data**

Order number	130030 11/16-16
GTIN	4062406035112
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: UN
Tool material: HSS E
Standard: DIN 376
Threads per inch: 16
Thread \varnothing : 17.462 mm
Overall length L: 125 mm
Shank $\varnothing D_s$: 14 mm
Shank square \square : 11 mm
Tapping hole \varnothing : 16 mm

Technical description

Thread \varnothing	17.462 mm
Number of cutting edges Z	3
Threads per inch	16
Shank $\varnothing D_s$	14 mm
Tapping hole \varnothing	16 mm
Thread pitch	1.588 mm
Overall length L	125 mm

Thread depth	34.92 mm
Number of clamping slots	3
Standard	DIN 376
Tool material	HSS E
Shank square <input type="checkbox"/>	11 mm
Thread type	UN
Thread size	11/16-16 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap