

Garant
Through hole machine tap, uncoated, Type: 11/16-20

Order data

Order number	130030 11/16-20
GTIN	4062406035105
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UN
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 20
 Thread \varnothing : 17.462 mm
 Overall length L: 125 mm
 Shank \varnothing D_s: 14 mm
 Shank square \square : 11 mm
 Tapping hole \varnothing : 16.25 mm

Technical description

Shank \varnothing D _s	14 mm
Number of cutting edges Z	3
Thread pitch	1.27 mm
Threads per inch	20
Overall length L	125 mm
Shank square \square	11 mm
Number of clamping slots	3

Tool material	HSS E
Thread Ø	17.462 mm
Tapping hole Ø	16.25 mm
Thread depth	34.92 mm
Standard	DIN 376
Thread type	UN
Thread size	11/16-20 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap