

Garant
Spiral flute machine tap, TiN, MF: M32X1,5

Order data

Order number	130015 M32X1,5
GTIN	4062406020446
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Technical description

Thread depth	80 mm
Tool material	HSS E
Shank square <input type="checkbox"/>	20 mm
Shank $\varnothing D_s$	25 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H

Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread Ø	32 mm
Tapping hole Ø	30.5 mm
Number of clamping slots	4
Standard	DIN 376
Overall length L	180 mm
Thread pitch	1.5 mm
Number of cutting edges Z	4
Thread type	M
Thread size	M32×1.5
Coating	TiN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap