

**Garant**
**Left-hand thread through hole machine tap, uncoated, Type: NO.2-64**

**Order data**

Order number	130031 NO.2-64
GTIN	4062406036508
Item class	10N

**Description**
**Note:**

Delivery time: 91 calendar days

Minimum order quantity: 25 pcs.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 64

Thread  $\varnothing$ : 2.18 mm

Overall length L: 45 mm

Shank  $\varnothing$  D<sub>s</sub>: 2.8 mm

Shank square  $\square$ : 2.1 mm

Tapping hole  $\varnothing$ : 1.9 mm

**Technical description**

Thread depth	6.54 mm
Thread pitch	0.399 mm
Overall length L	45 mm
Tapping hole $\varnothing$	1.9 mm
Thread $\varnothing$	2.18 mm
Threads per inch	64
Shank square $\square$	2.1 mm

Shank $\varnothing D_s$	2.8 mm
Number of cutting edges Z	3
Standard	DIN 371
Tool material	HSS E
Number of clamping slots	3
Thread type	UNF-LH
Thread size	2-64 UNF LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap