

Garant
Through hole machine tap, TiN, Type: 2-20

Order data

Order number	130035 2-20
GTIN	4062406040888
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread \varnothing : 50.8 mm

Overall length L: 250 mm

Shank \varnothing D_s: 40 mm

Shank square \square : 32 mm

Tapping hole \varnothing : 49.58 mm

Technical description

Number of cutting edges Z	4
Thread \varnothing	50.8 mm
Tapping hole \varnothing	49.58 mm
Thread pitch	1.27 mm
Tool material	HSS E
Shank square \square	32 mm
Thread depth	101.6 mm
Overall length L	250 mm

Number of clamping slots	4
Threads per inch	20
Shank $\varnothing D_s$	40 mm
Standard	DIN 376
Thread type	UN
Thread size	2-20 UN
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap