

Garant
Through hole machine tap, TiN, Type: 1/2-16

Order data

Order number	130035 1/2-16
GTIN	4062406039387
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UN
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 16
 Thread Ø: 12.7 mm
 Overall length L: 110 mm
 Shank Ø D_s: 11 mm
 Shank square □: 9 mm
 Tapping hole Ø: 11.2 mm

Technical description

Thread depth	25.4 mm
Threads per inch	16
Number of clamping slots	3
Shank Ø D _s	11 mm
Number of cutting edges Z	3
Tool material	HSS E
Thread Ø	12.7 mm
Overall length L	110 mm

Tapping hole Ø	11.2 mm
Standard	DIN 376
Thread pitch	1.588 mm
Shank square □	9 mm
Thread type	UN
Thread size	1/2-16 UN
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap