

**Garant**
**Through hole machine tap, TiN, Type: 5/16-20**

**Order data**

Order number	130035 5/16-20
GTIN	4062406039158
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 3 pcs.  
 Special / custom-made product - return not possible  
 Thread type: UN  
 Tool material: HSS E  
 Standard: DIN 371  
 Threads per inch: 20  
 Thread  $\varnothing$ : 7.94 mm  
 Overall length L: 90 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 8 mm  
 Shank square  $\square$ : 6.2 mm  
 Tapping hole  $\varnothing$ : 6.7 mm

**Technical description**

Thread pitch	1.27 mm
Number of cutting edges Z	3
Shank square $\square$	6.2 mm
Overall length L	90 mm
Standard	DIN 371
Number of clamping slots	3
Shank $\varnothing$ D <sub>s</sub>	8 mm

Tapping hole Ø	6.7 mm
Threads per inch	20
Thread Ø	7.94 mm
Tool material	HSS E
Thread depth	23.82 mm
Thread type	UN
Thread size	5/16-20 UN
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap