

Garant**Through hole machine tap, TiN, Type: 1.3/16-8****Order data**

Order number	130035 1.3/16-8
GTIN	4062406040109
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 8

Thread \varnothing : 30.162 mm

Overall length L: 180 mm

Shank \varnothing D_s: 22 mmShank square \square : 18 mmTapping hole \varnothing : 27.2 mm**Technical description**

Standard	DIN 376
Overall length L	180 mm
Thread pitch	3.175 mm
Tool material	HSS E
Number of cutting edges Z	4
Threads per inch	8
Thread \varnothing	30.162 mm

Thread depth	60.32 mm
Number of clamping slots	4
Shank square □	18 mm
Shank Ø D _s	22 mm
Tapping hole Ø	27.2 mm
Thread type	UN
Thread size	1.3/16-8 UN
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap