

**Garant**
**Left-hand thread through hole machine tap, TiN, Type: 1.1/8-14**

**Order data**

Order number	130036 1.1/8-14
GTIN	4062406042264
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UNS-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 14  
 Thread  $\varnothing$ : 28.575 mm  
 Overall length L: 180 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 22 mm  
 Shank square  $\square$ : 18 mm  
 Tapping hole  $\varnothing$ : 27 mm

**Technical description**

Thread pitch	1.814 mm
Shank square $\square$	18 mm
Tapping hole $\varnothing$	27 mm
Tool material	HSS E
Threads per inch	14
Number of cutting edges Z	4
Thread $\varnothing$	28.575 mm
Standard	DIN 376

Number of clamping slots	4
Overall length L	180 mm
Shank $\varnothing D_s$	22 mm
Thread depth	57.15 mm
Thread type	UNS-LH
Thread size	1.1/8-14 UNS LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap