

Garant**Through hole machine tap, TiN, Type: 13/16-20****Order data**

Order number	130035 13/16-20
GTIN	4062406039691
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNEF

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread \varnothing : 20.638 mm

Overall length L: 140 mm

Shank \varnothing D_s: 18 mmShank square \square : 14.5 mmTapping hole \varnothing : 19.6 mm**Technical description**

Thread pitch	1.27 mm
Overall length L	140 mm
Tapping hole \varnothing	19.6 mm
Standard	DIN 376
Shank square \square	14.5 mm
Number of cutting edges Z	3
Thread \varnothing	20.638 mm

Threads per inch	20
Thread depth	41.3 mm
Number of clamping slots	3
Shank $\varnothing D_s$	18 mm
Tool material	HSS E
Thread type	UNEF
Thread size	13/16-20 UNEF
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap