

**Garant**
**Spiral flute machine tap, TiN, MF: M48X3**

**Order data**

Order number	130015 M48X3
GTIN	4062406021481
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: M  
 Tool material: HSS E  
 Standard: DIN 376  
 Tolerance class: ISO 1 4H  
 Tolerance class: ISO 1X 4HX  
 Tolerance class: ISO 2 6H  
 Thread pitch: 3 mm  
 Overall length L: 250 mm  
 Shank  $\varnothing D_s$ : 36 mm  
 Shank square  $\square$ : 29 mm  
 Tapping hole  $\varnothing$ : 45 mm

**Technical description**

Thread $\varnothing$	48 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05

Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread pitch	3 mm
Number of cutting edges Z	4
Tapping hole Ø	45 mm
Shank Ø D <sub>s</sub>	36 mm
Shank square □	29 mm
Overall length L	250 mm
Number of clamping slots	4
Standard	DIN 376
Tool material	HSS E
Thread depth	120 mm
Thread type	M
Thread size	M48×3
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap