

Garant
Left-hand thread through hole machine tap, TiN, Type: 1.1/2-12

Order data

Order number	130036 1.1/2-12
GTIN	4062406042677
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread Ø: 38.1 mm

Overall length L: 200 mm

Shank Ø D_s: 32 mm

Shank square □: 24 mm

Tapping hole Ø: 36 mm

Technical description

Thread Ø	38.1 mm
Shank Ø D _s	32 mm
Shank square □	24 mm
Thread depth	76.2 mm
Overall length L	200 mm
Threads per inch	12
Standard	DIN 376
Tapping hole Ø	36 mm

Number of cutting edges Z	4
Thread pitch	2.117 mm
Number of clamping slots	4
Tool material	HSS E
Thread type	UNF-LH
Thread size	1.1/2-12 UNF LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap