

Garant
Through hole machine tap, TiN, Type: 0,390-27

Order data

Order number	130035 0,390-27
GTIN	4062406039257
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 371

Threads per inch: 27

Thread \varnothing : 9.906 mm

Overall length L: 100 mm

Shank \varnothing D_s: 10 mm

Shank square \square : 8 mm

Tapping hole \varnothing : 9 mm

Technical description

Thread pitch	0.94 mm
Thread \varnothing	9.906 mm
Shank \varnothing D _s	10 mm
Standard	DIN 371
Tool material	HSS E
Shank square \square	8 mm
Tapping hole \varnothing	9 mm
Thread depth	19.812 mm

Number of clamping slots	3
Threads per inch	27
Number of cutting edges Z	3
Overall length L	100 mm
Thread type	UNS
Thread size	0.390-27
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap