

**Garant**
**Left-hand thread blind hole machine tap, TiN, MF: M10X1,5**

**Order data**

Order number	130016 M10X1,5
GTIN	4062406022365
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 3 pcs.  
 Special / custom-made product - return not possible  
 Thread type: M-LH  
 Tool material: HSS E  
 Standard: DIN 371  
 Tolerance class: ISO 1 4H  
 Tolerance class: ISO 1X 4HX  
 Tolerance class: ISO 2 6H  
 Thread pitch: 1.5 mm  
 Overall length L: 100 mm  
 Shank  $\varnothing D_s$ : 10 mm  
 Shank square  $\square$ : 8 mm  
 Tapping hole  $\varnothing$ : 8.5 mm

**Technical description**

Number of cutting edges Z	3
Standard	DIN 371
Thread $\varnothing$	10 mm
Thread depth	25 mm
Shank square $\square$	8 mm
Thread pitch	1.5 mm

Tapping hole Ø	8.5 mm
Overall length L	100 mm
Shank Ø D <sub>s</sub>	10 mm
Number of clamping slots	3
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tool material	HSS E
Thread type	M-LH
Thread size	M10×1.5
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap