

**Garant**
**Spiral flute machine tap, TiN, MF: M8X0,35**

**Order data**

Order number	130015 M8X0,35
GTIN	4062406018627
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

**Technical description**

Overall length L	90 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX

Tolerance class	6H +0.10
Number of clamping slots	3
Shank $\varnothing D_s$	8 mm
Thread $\varnothing$	8 mm
Number of cutting edges Z	3
Shank square $\square$	6.2 mm
Standard	DIN 371
Tool material	HSS E
Tapping hole $\varnothing$	7.65 mm
Thread pitch	0.35 mm
Thread depth	20 mm
Thread type	M
Thread size	M8×0.35
Coating	TiN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap