

Garant
Through hole machine tap, TiN, Type: 1.13/16-8

Order data

Order number	130035 1.13/16-8
GTIN	4062406040765
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UN
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 8
 Thread \varnothing : 46.037 mm
 Overall length L: 250 mm
 Shank \varnothing D_s: 36 mm
 Shank square \square : 29 mm
 Tapping hole \varnothing : 43 mm

Technical description

Thread \varnothing	46.037 mm
Number of clamping slots	4
Standard	DIN 376
Threads per inch	8
Tapping hole \varnothing	43 mm
Number of cutting edges Z	4
Thread depth	92 mm

Shank $\varnothing D_s$	36 mm
Overall length L	250 mm
Thread pitch	3.175 mm
Shank square \square	29 mm
Tool material	HSS E
Thread type	UN
Thread size	1.13/16-8 UN
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap