

Garant
Through hole machine tap, TiN, Type: 1/2-27

Order data

Order number	130035 1/2-27
GTIN	4062406039349
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 27

Thread Ø: 12.7 mm

Overall length L: 110 mm

Shank Ø D_s: 11 mm

Shank square □: 9 mm

Tapping hole Ø: 11.85 mm

Technical description

Tool material	HSS E
Number of clamping slots	3
Thread pitch	0.94 mm
Standard	DIN 376
Number of cutting edges Z	3
Threads per inch	27
Tapping hole Ø	11.85 mm
Thread depth	25.4 mm

Thread Ø	12.7 mm
Overall length L	110 mm
Shank Ø D _s	11 mm
Shank square □	9 mm
Thread type	UNS
Thread size	1/2-27 UNS
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap