

Garant
Left-hand thread blind hole machine tap, TiN, MF: M10X0,35

Order data

| | |
|--------------|-----------------|
| Order number | 130016 M10X0,35 |
| GTIN | 4062406022310 |
| Item class | 10N |

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.35 mm

Overall length L: 100 mm

Shank \varnothing D_s: 10 mm

Shank square □: 8 mm

Tapping hole \varnothing : 9.65 mm

Technical description

| | |
|-----------------|------------|
| Standard | DIN 371 |
| Tolerance class | ISO 1 4H |
| Tolerance class | ISO 1X 4HX |
| Tolerance class | ISO 2 6H |
| Tolerance class | ISO 2X 6HX |
| Tolerance class | 6H +0.05 |

| | |
|----------------------------------|--|
| Tolerance class | 6H +0.20 |
| Tolerance class | ISO 3 6G |
| Tolerance class | ISO 3X 6GX |
| Tolerance class | 7H |
| Tolerance class | 7HX |
| Tolerance class | 7G |
| Tolerance class | 7GX |
| Tolerance class | 6H +0.10 |
| Thread pitch | 0.35 mm |
| Tool material | HSS E |
| Shank square \square | 8 mm |
| Number of clamping slots | 3 |
| Overall length L | 100 mm |
| Number of cutting edges Z | 3 |
| Tapping hole \varnothing | 9.65 mm |
| Shank $\varnothing D_s$ | 10 mm |
| Thread \varnothing | 10 mm |
| Thread depth | 25 mm |
| Thread type | MF-LH |
| Thread size | M10x0.35 |
| Coating | TiN |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2xD for blind holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |

| | |
|-----------------|---------|
| Colour ring | without |
| Type of product | Tap |