

Garant**Left-hand thread blind hole machine tap, TiN, MF: M3,5X0,6****Order data**

Order number	130016 M3,5X0,6
GTIN	4062406022020
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: M-LH

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.6 mm

Overall length L: 56 mm

Shank $\varnothing D_s$: 4 mm

Shank square \square : 3 mm

Tapping hole \varnothing : 2.9 mm

Technical description

Thread pitch	0.6 mm
Shank square \square	3 mm
Shank $\varnothing D_s$	4 mm
Overall length L	56 mm
Standard	DIN 371
Tapping hole \varnothing	2.9 mm

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Number of cutting edges Z	3
Thread Ø	3.5 mm
Thread depth	8.75 mm
Tool material	HSS E
Number of clamping slots	3
Thread type	M-LH
Thread size	M3.5×0.6
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap