

**Garant**
**Through hole machine tap, TiN, Type: 11/16-16**

**Order data**

Order number	130035 11/16-16
GTIN	4062406039592
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread  $\varnothing$ : 17.462 mm

Overall length L: 125 mm

Shank  $\varnothing$  D<sub>s</sub>: 14 mm

Shank square  $\square$ : 11 mm

Tapping hole  $\varnothing$ : 16 mm

**Technical description**

Threads per inch	16
Shank $\varnothing$ D <sub>s</sub>	14 mm
Number of clamping slots	3
Thread pitch	1.588 mm
Tool material	HSS E
Shank square $\square$	11 mm
Thread depth	34.92 mm

Thread Ø	17.462 mm
Standard	DIN 376
Tapping hole Ø	16 mm
Number of cutting edges Z	3
Overall length L	125 mm
Thread type	UN
Thread size	11/16-16 UN
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap