

Garant
Through hole machine tap, TiN, Type: 1.3/8-8

Order data

Order number	130035 1.3/8-8
GTIN	4062406040314
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 8

Thread \varnothing : 34.925 mm

Overall length L: 200 mm

Shank \varnothing D_s : 28 mm

Shank square \square : 22 mm

Tapping hole \varnothing : 31.9 mm

Technical description

Number of clamping slots	4
Thread \varnothing	34.925 mm
Overall length L	200 mm
Tapping hole \varnothing	31.9 mm
Shank \varnothing D_s	28 mm
Shank square \square	22 mm
Tool material	HSS E
Thread pitch	3.175 mm

Number of cutting edges Z	4
Threads per inch	8
Standard	DIN 376
Thread depth	69.85 mm
Thread type	UN
Thread size	1.3/8-8 UN
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap