

Garant
Left-hand thread through hole machine tap, uncoated, Type: 1.1/16-16

Order data

Order number	130031 1.1/16-16
GTIN	4062406037710
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread \varnothing : 26.988 mm

Overall length L: 160 mm

Shank \varnothing D_s: 20 mm

Shank square \square : 16 mm

Tapping hole \varnothing : 25.5 mm

Technical description

Number of clamping slots	4
Shank square \square	16 mm
Thread \varnothing	26.988 mm
Thread pitch	1.588 mm
Tool material	HSS E
Shank \varnothing D _s	20 mm
Threads per inch	16

Overall length L	160 mm
Standard	DIN 376
Tapping hole Ø	25.5 mm
Number of cutting edges Z	4
Thread depth	54 mm
Thread type	UN-LH
Thread size	1.1/16-16 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap