

**Garant**
**Left-hand thread through hole machine tap, uncoated, Type: 1.7/16-12**

**Order data**

Order number	130031 1.7/16-12
GTIN	4062406038120
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UN-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 12  
 Thread  $\varnothing$ : 36.512 mm  
 Overall length L: 200 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 28 mm  
 Shank square □: 22 mm  
 Tapping hole  $\varnothing$ : 34.5 mm

**Technical description**

Threads per inch	12
Overall length L	200 mm
Number of clamping slots	4
Thread depth	73 mm
Number of cutting edges Z	4
Tapping hole $\varnothing$	34.5 mm
Shank $\varnothing$ D <sub>s</sub>	28 mm

Shank square □	22 mm
Tool material	HSS E
Thread pitch	2.117 mm
Standard	DIN 376
Thread Ø	36.512 mm
Thread type	UN-LH
Thread size	1.7/16-12 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap