

Garant
Through hole machine tap, uncoated, Type: 9/16-14

Order data

Order number	130030 9/16-14
GTIN	4062406034993
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNS
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 14
 Thread \varnothing : 14.29 mm
 Overall length L: 110 mm
 Shank \varnothing D_s: 11 mm
 Shank square □: 9 mm
 Tapping hole \varnothing : 12.6 mm

Technical description

Number of clamping slots	3
Shank \varnothing D _s	11 mm
Tool material	HSS E
Thread \varnothing	14.29 mm
Thread pitch	1.814 mm
Overall length L	110 mm
Tapping hole \varnothing	12.6 mm

Shank square □	9 mm
Thread depth	57.16 mm
Standard	DIN 376
Number of cutting edges Z	3
Threads per inch	14
Thread type	UNS
Thread size	9/16-14 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap