

Garant**Left-hand thread through hole machine tap, uncoated, Type: 3/4-18****Order data**

Order number	130031 3/4-18
GTIN	4062406037406
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 18

Thread Ø: 19.05 mm

Overall length L: 125 mm

Shank Ø D_s: 14 mm

Shank square □: 11 mm

Tapping hole Ø: 17.75 mm

Technical description

Shank Ø D _s	14 mm
Overall length L	125 mm
Shank square □	11 mm
Thread pitch	1.411 mm
Number of clamping slots	3
Tapping hole Ø	17.75 mm
Thread depth	57.15 mm

Standard	DIN 376
Threads per inch	18
Thread Ø	19.05 mm
Tool material	HSS E
Number of cutting edges Z	3
Thread type	UNS-LH
Thread size	3/4-18 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap