

Garant**Left-hand thread through hole machine tap, TiN, Type: 9/16-24****Order data**

Order number	130036 9/16-24
GTIN	4062406041670
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNEF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread \varnothing : 14.29 mm

Overall length L: 110 mm

Shank \varnothing D_s: 11 mmShank square \square : 9 mmTapping hole \varnothing : 13.4 mm**Technical description**

Thread \varnothing	14.29 mm
Thread depth	57.16 mm
Tapping hole \varnothing	13.4 mm
Threads per inch	24
Number of clamping slots	3
Thread pitch	1.058 mm
Shank \varnothing D _s	11 mm

Standard	DIN 376
Number of cutting edges Z	3
Tool material	HSS E
Shank square □	9 mm
Overall length L	110 mm
Thread type	UNEF-LH
Thread size	9/16-24 UNEF LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap