

Garant**Through hole machine tap, TiN, Type: 7/16-24****Order data**

Order number	130035 7/16-24
GTIN	4062406039288
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread \varnothing : 11.11 mm

Overall length L: 110 mm

Shank \varnothing D_s: 9 mmShank square \square : 7 mmTapping hole \varnothing : 10.1 mm**Technical description**

Thread \varnothing	11.11 mm
Thread pitch	1.058 mm
Shank square \square	7 mm
Tapping hole \varnothing	10.1 mm
Tool material	HSS E
Shank \varnothing D _s	9 mm
Threads per inch	24

Number of cutting edges Z	3
Number of clamping slots	3
Standard	DIN 376
Thread depth	33.33 mm
Overall length L	110 mm
Thread type	UNS
Thread size	7/16-24 UNS
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap