

Garant
Through hole machine tap, uncoated, Type: 1.7/8-10

Order data

Order number	130030 1.7/8-10
GTIN	4062406036348
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UNS
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 10
 Thread \varnothing : 47.625 mm
 Overall length L: 250 mm
 Shank \varnothing D_s: 36 mm
 Shank square \square : 29 mm
 Tapping hole \varnothing : 45.3 mm

Technical description

Threads per inch	10
Shank \varnothing D _s	36 mm
Thread pitch	2.54 mm
Thread \varnothing	47.625 mm
Shank square \square	29 mm
Tapping hole \varnothing	45.3 mm
Overall length L	250 mm
Thread depth	95.25 mm

Number of cutting edges Z	4
Tool material	HSS E
Standard	DIN 376
Number of clamping slots	4
Thread type	UNS
Thread size	1.7/8-10 UNS
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap