

**Garant****Left-hand thread through hole machine tap, TiN, Type: 5/8-11****Order data**

Order number	130036 5/8-11
GTIN	4062406041809
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNC-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 11

Thread Ø: 15.88 mm

Overall length L: 110 mm

Shank Ø D<sub>s</sub>: 12 mm

Shank square □: 9 mm

Tapping hole Ø: 13.53 mm

**Technical description**

Threads per inch	11
Shank Ø D <sub>s</sub>	12 mm
Number of cutting edges Z	3
Thread pitch	2.309 mm
Tapping hole Ø	13.53 mm
Number of clamping slots	3
Thread depth	47.64 mm

Tool material	HSS E
Overall length L	110 mm
Thread Ø	15.88 mm
Shank square □	9 mm
Standard	DIN 376
Thread type	UNC-LH
Thread size	5/8-11 UNC LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap