

Garant**Through hole machine tap, uncoated, Type: 3/4-24****Order data**

Order number	130030 3/4-24
GTIN	4062406035143
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread Ø: 19.05 mm

Overall length L: 125 mm

Shank Ø D_s: 14 mm

Shank square □: 11 mm

Tapping hole Ø: 18.1 mm

Technical description

Thread pitch	1.058 mm
Shank square □	11 mm
Thread depth	57.15 mm
Thread Ø	19.05 mm
Number of cutting edges Z	3
Tapping hole Ø	18.1 mm
Overall length L	125 mm

Threads per inch	24
Shank $\varnothing D_s$	14 mm
Tool material	HSS E
Number of clamping slots	3
Standard	DIN 376
Thread type	UNS
Thread size	3/4-24 UNS
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap