

Garant**Left-hand thread through hole machine tap, uncoated, Type: 1.3/16-16****Order data**

Order number	130031 1.3/16-16
GTIN	4062406037840
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread \varnothing : 30.162 mm

Overall length L: 180 mm

Shank \varnothing D_s: 22 mmShank square \square : 18 mmTapping hole \varnothing : 28.7 mm**Technical description**

Threads per inch	16
Number of clamping slots	4
Thread \varnothing	30.162 mm
Standard	DIN 376
Overall length L	180 mm
Thread depth	60.32 mm
Tapping hole \varnothing	28.7 mm

Shank square □	18 mm
Shank $\varnothing D_s$	22 mm
Thread pitch	1.588 mm
Number of cutting edges Z	4
Tool material	HSS E
Thread type	UN-LH
Thread size	1.3/16-16 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap